

SENSITITRE™ MYCOBACTERIA PLATE FORMAT

Plate Code: **SLOMYCO**

	1	2	3	4	5	6	7	8	9	10	11	12
A	CLA 0.06	CLA 0.12	CLA 0.25	CLA 0.5	CLA 1	CLA 2	CLA 4	CLA 8	CIP 16	STR 64	DOX 16	ETH 20
B	CLA 16	CLA 32	CLA 64	MXF 8	RIF 8	SXT 8/152	AMI 64	LZD 64	CIP 8	STR 32	DOX 8	ETH 10
C	RFB 8	EMB 16	INH 8	MXF 4	RIF 4	SXT 4/76	AMI 32	LZD 32	CIP 4	STR 16	DOX 4	ETH 5
D	RFB 4	EMB 8	INH 4	MXF 2	RIF 2	SXT 2/38	AMI 16	LZD 16	CIP 2	STR 8	DOX 2	ETH 2.5
E	RFB 2	EMB 4	INH 2	MXF 1	RIF 1	SXT 1/19	AMI 8	LZD 8	CIP 1	STR 4	DOX 1	ETH 1.2
F	RFB 1	EMB 2	INH 1	MXF 0.5	RIF 0.5	SXT 0.5/9.5	AMI 4	LZD 4	CIP 0.5	STR 2	DOX 0.5	ETH 0.6
G	RFB 0.5	EMB 1	INH 0.5	MXF 0.25	RIF 0.25	SXT 0.25/4.75	AMI 2	LZD 2	CIP 0.25	STR 1	DOX 0.25	ETH 0.3
H	RFB 0.25	EMB 0.5	INH 0.25	MXF 0.12	RIF 0.12	SXT 0.12/2.38	AMI 1	LZD 1	CIP 0.12	STR 0.5	DOX 0.12	POS

ANTIMICROBICS

CLA	Clarithromycin
RFB	Rifabutin
EMB	Ethambutol
INH	Isoniazid
MXF	Moxifloxacin
RIF	Rifampin
SXT	Trimethoprim / sulfamethoxazole
AMI	Amikacin
LZD	Linezolid
CIP	Ciprofloxacin
STR	Streptomycin
DOX	Doxycycline
ETH	Ethionamide
POS	Positive Control