

## Affymetrix' tools for model organism research

Affymetrix provides an extensive range of microarray analysis tools for model organism genomics researchers performing expression analysis, whole-transcript profiling, and genotyping studies. If the organism you are studying is not on this list, please contact us to learn more about our custom program.

Organism	Application			
	3' IVT expression	WT expression	Genotyping	Tiling
<i>Arabidopsis</i>	●	●	●+	●
<i>Aspergillus niger, oryzae, and nidulans</i>	●+			
<i>Axolotl</i>	●+			
<i>Brachypodium</i>		●+		●+
<i>Brassica</i>		●+		
<i>Caenorhabditis elegans</i>	●	●		●
Canine	●**	●	●+	
Chicken	●	●	●	
Cynomolgus macaque		●		
<i>Drosophila (melanogaster, simulans, yokuba)</i>	●	●		●
<i>E coli</i>	●			●
Feline		●		
Guinea pig		●		
Marmoset		●		
Mouse	●	●	●	●
Porcine	●	●		
Rabbit		●		
Rat	●	●	●	
Rhesus macaque	●	●		
<i>Rhodobacter sphaeroides</i>	●			
<i>Saccharomyces cerevisiae</i>	●			●
<i>Schizosaccharomyces pombe</i>	●			●
<i>Xenopus laevis</i>	●			
<i>Xenopus tropicalis</i>	●			
Zebra Finch		●		
Zebrafish	●	●		

\*\*Available in cartridge and plate formats. +Consortia array: please contact your local account manager for minimum order size requirements.

Affymetrix, Inc. Tel: +1-888-362-2447 ■ Affymetrix UK Ltd. Tel: +44-(0)-1628-552550 ■ Affymetrix Japan K.K. Tel: +81-(0)3-6430-4020  
Panomics Solutions Tel: +1-877-726-6642 panomics.affymetrix.com ■ USB Products Tel: +1-800-321-9322 usb.affymetrix.com

[www.affymetrix.com](http://www.affymetrix.com) Please visit our website for international distributor contact information.

**For Research Use Only. Not for use in diagnostic procedures.**

P/N EMI05047 Rev. 1

©Affymetrix, Inc. All rights reserved. Affymetrix®, Axiom®, Command Console®, CytoScan®, DMET™, GeneAtlas®, GeneChip®, GeneChip-compatible™, GeneTitan®, Genotyping Console™, myDesign™, NetAffx®, OncoScan®, Powered by Affymetrix™, PrimeView™, Procarta®, and QuantiGene® are trademarks or registered trademarks of Affymetrix, Inc. All other trademarks are the property of their respective owners.

Products may be covered by one or more of the following patents: U.S. Patent Nos. 5,445,934; 5,744,305; 5,945,334; 6,140,044; 6,399,365; 6,420,169; 6,551,817; 6,733,977; 7,629,164; 7,790,389 and D430,024 and other U.S. or foreign patents. Products are manufactured and sold under license from OGT under 5,700,637 and 6,054,270.