



**Comments for pENTR™/U6**  
2854 nucleotides

*rrnB* T2 transcription terminator: bases 268-295 (C)

*rrnB* T1 transcription terminator: bases 427-470

M13 forward (-20) priming site: bases 537-552

*attL*1: bases 569-668 (C)

U6 promoter: bases 705-968

U6 forward priming site: bases 890-909

5' overhang: bases 965-968 (C)

5' overhang: bases 969-972

Pol III transcription terminator: bases 969-974

*attL*2: bases 979-1078

M13 reverse priming site: bases 1119-1135

Kanamycin resistance gene: bases 1248-2057

pUC origin: bases 2178-2851

(C) = complementary strand