

## Value Lab Refrigerators, Freezers and Combination Units

An economical solution for safe sample storage.

Thermo Scientific Value laboratory refrigerators, freezers and combination units are particularly suited for routine laboratory applications with sizes ranging from undercounter to full-height freestanding. Our features are not available in domestic models and meet the demanding requirements of the laboratory environment.

**Not available in North America, consult your sales representative for availability.**

**Alert: These units are not intended for critical lab samples.**

Storage of high value, life science materials or clinical biologicals may require alarm, monitoring, back-up and temperature performance features. The need to add these features should be determined by your industrial hygienist or safety officer. These units are not suitable for corrosive environments.

- Factory tested prior to shipment
- NRTL listed
- Environmentally-friendly, non CFC refrigerants
- Adjustable temperature control
- Easy-to-clean, durable finish
- Manual and auto defrost combination units
- Manual defrost refrigerators and freezers

**Warranty: 13 months parts and labor**



**Model No: 20LFEETSV**  
591.82 liter lab freezer

## Thermo Scientific Value Lab Refrigerators (Temperature Range: 1° to 12°C)

Model No.	Capacity	Interior Storage	Voltage	Exterior Dimensions: (H x W x D)	Interior Dimensions: (H x W x D)	Shipping Weight
05LREETSV	5.5 cu. ft. (155.7 liters)	3 adjustable shelves	230V/50hz	33.5" x 23.63" x 23.5" (85.1 x 61 x 60 cm)	27.75" x 20" x 17.5" (70.5 x 50.8 x 44.5 cm)	100 lbs. (45.3kg)

## Thermo Scientific Value Lab Freezers (Temperature Range -12° to -20°C)

Model No.	Capacity	Interior Storage	Voltage	Exterior Dimensions: (H x W x D)	Interior Dimensions: (H x W x D)	Shipping Weight
20LFEETSV	20.9 cu. ft. (591.82 liters)	4 fixed shelves, 6 door shelves	230V/50hz	73.13" x 34" x 32.13" (185.7 x 86.4 x 81.6 cm)	57.8" x 27.8" x 23.8" (146.7 x 70.49 x 60.3 cm)	198 lbs. (89.9 kg)

## Thermo Scientific Combination Lab Refrigerator/Freezers (Temperature Range: 1° to 12°C [ref], -12° to -20°C [frz])

Model No.	Capacity	Interior Storage	Voltage	Exterior Dimensions: (H x W x D)	Interior Dimensions: (H x W x D)	Shipping Weight
05LCEETSV	5.6 cu. ft. (158.6 liters)	2 adjustable shelves, 1 drawer, 3 door shelves	230V/50hz	33.5" x 23.63" x 23.5" (85.1 x 60 x 59.7 cm)	Ref: 19.5" x 20.5" x 17" (49.5 x 52.1 x 43.2 cm), Frz: 5" x 19" x 11.5" (12.7 x 48.3 x 29.2 cm)	120 lbs. (54.5 kg)
10LCEETSV	10.1 cu. ft. (286.0 liters)	3 adjustable shelves, 1 fixed shelf, 1 drawer, 4 door shelves	230V/50hz	59.75" x 23.63" x 24" (151.77 x 60 x 60.96 cm)	Ref: 38.25" x 19.75" x 18.25" (97.2 x 50.2 x 46.4 cm); Frz: 11.25" x 18" x 18.25" (28.6 x 45.7 x 46.4 cm)	150 lbs. (68 kg)

Find out more at [thermofisher.com/cold](http://thermofisher.com/cold)

**ThermoFisher**  
SCIENTIFIC