

Value Lab Refrigerators, Freezers and Combination Units

An economical solution for safe sample storage.

Thermo Scientific Value laboratory refrigerators, freezers and combination units are particularly suited for routine laboratory applications with sizes ranging from small benchtop to full-height freestanding. Our features are not available in domestic models and meet the demanding requirements of the laboratory environment.

Available in North America and select countries, consult your sales representative for availability.

Alert: These units are not intended for critical lab samples.

Storage of high value, life science materials or clinical biologicals may require alarm, monitoring, back-up and temperature performance features. The need to add these features should be determined by your industrial hygienist or safety officer. These units are not suitable for corrosive environments.

- Factory tested prior to shipment
- NRTL listed
- Environmentally-friendly, non CFC refrigerants
- Adjustable temperature control
- Easy-to-clean, durable finish
- Manual and auto defrost combination units
- Manual defrost refrigerators and freezers

Warranty: 13 months parts and labor



Model No: 20LFEETSA
20.9 cu. ft. lab freezer



Model No: 05LREETSA
5.5 cu. ft. lab refrigerator



Model No: 25LCEETSA
23.2 cu. ft. combination refrigerator and freezer

Thermo Scientific Value Lab Refrigerators (Temperature Range 1° to 12°C, 1°C to 8°C on 02LREETSA)

Model No.	Capacity	Interior Storage	Voltage	Exterior Dimensions: (H x W x D)	Interior Dimensions: (H x W x D)	Agency Listing	Shipping Weight
02LREETSA	1.8 cu. ft. (51.0 liters)	1 removable shelf, storage on bottom	115V/60Hz	19" x 18.63" x 17.25" (48.3 x 47.3 x 43.8 cm)	15.5" x 16" x 14" (39.4 x 40.6 x 35.6 cm)	cULus	55 lbs. (24.9 kg)
05LREETSA	5.5 cu. ft. (155.7 liters)	3 adjustable shelves, storage on bottom	115V/60Hz	33.5" x 23.63" x 23.5" (85.1 x 60 x 60 cm)	27.75" x 20" x 17.5" (70.5 x 50.8 x 44.5 cm)	cULus	100lbs. (45.3kg)
20LREETSA	20.3 cu. ft. (574.8 liters)	4 fixed interior shelves, 6 door shelves	115V/60Hz	73.13" x 34" x 32.13" (185.7 x 86.4 x 81.6 cm)	57.8" x 27.8" x 23.8" (146.7 x 70.49 x 60.3 cm)	cCSAus	283 lbs. (128 kg)

Thermo Scientific Value Lab Freezers (Temperature Range -12° to -24°C on 02LFEETSA and 05LFEETSA, -12° to -20°C on Other Freezers)

Model No.	Capacity	Interior Storage	Voltage	Exterior Dimensions: (H x W x D)	Interior Dimensions: (H x W x D)	Agency Listing	Shipping Weight
02LFEETSA	1.8 cu. ft. (51 liters)	2 wire shelves	115V/60Hz	24.5" x 18.5" x 17.75" (62.23 x 46.99 x 45.09 cm)	18.63" x 13.38" x 13" (47.32 x 33.99 x 33.02 cm)	cULus	43 lbs. (19.5 kg)
04LFEETSA	3.5 cu. ft. (99.0 liters)	3 drawers	115V/60Hz	33.5" x 23.63" x 23.5" (85.1 x 61 x 60 cm)	24.25" x 17.75" x 16.5" (61.6 x 45.09 x 41.9 cm)	cULus	120 lbs. (54.5kg)
05LFEETSA	5.0 cu. ft. (141.6 liters)	2 fixed interior, 3 door shelves	115V/60Hz	33.13" x 21.38" x 25.75" (84.15 x 54.3 x 65.4 cm)	29.5" x 18.63" x 19" (74.9 x 47.32 x 48.2 cm)	cULus	95 lbs. (43 kg)
20LFEETSA	20.9 cu. ft. 591.82 (liters)	4 fixed shelves, 6 door shelves	115V/60Hz	73.13" x 34" x 32.13" (185.7 x 86.4 x 81.6 cm)	57.8" x 27.8" x 23.8" (146.7 x 70.49 x 60.3 cm)	cCSAus	198 lbs. (89.8 kg)

Thermo Scientific Value Combination Lab Refrigerator/Freezers (Temperature Range: 1° to 12°C [ref], -12° to -20°C [frz], 0° to 8°C [ref] and -6° to -20°C [frz] on 18LCEETSA, 1° to 12°C [ref] and -14° to -25°C [frz] on 25LCEETSA)

Model No.	Capacity	Interior Storage	Voltage	Exterior Dimensions: (H x W x D)	Interior Dimensions: (H x W x D)	Agency Listing	Shipping Weight
05LCEETSA	5.6 cu. ft. (158.6 liters)	2 adjustable shelves, 1 drawer, 3 door shelves	115V/60hz	33.5" x 23.63" x 23.5" (85.1 x 60 x 60 cm)	Ref: 19.5" x 20.5" x 17" (49.5 x 52.1 x 43.2 cm); Frz: 5" x 19" x 11.5" (12.7 x 48.3 x 29.2 cm)	cULus	120 lbs. (54.5 kg)
10LCEETSA	10.1 cu. ft. (286.0 liters)	3 adjustable shelves, 1 fixed shelf, 1 drawer, 4 door shelves	115V/60hz	59.75" x 23.63" x 24" (151.77 x 60 x 60.96 cm)	Ref: 38.25" x 19.75" x 18.25" (97.2 x 50.2 x 46.4 cm); Frz: 11.25" x 18" x 18.25" (28.6 x 45.7 x 46.4 cm)	cULus	150 lbs. (68 kg)
12LCEETSA	11.8 cu. ft. (334.1 liters)	Ref: 4 adjustable shelves; Frz: 3 drawers	115V/60hz	79" x 23.63" x 23.75" (200.7 x 60.02 x 63.5 cm)	Ref: 35.25" x 19.75" x 18.5" (89.5 x 50.2 x 46.99 cm); Frz: 25.38" x 17.13" x 15.5" (64.5 x 43.5 x 39.4 cm)	ETL	251 lbs. (113.9 kg)
18LCEETSA	18.0 cu. ft. (515.4 liters)	Ref: 2 adjustable, 1 fixed, 2 drawers, 3 door; Frz: 1 adjustable, 2 door	115V/60hz	66.63" x 30" x 30.13" (169.24 x 76.2 x 76.5 cm)	Ref: 39.75" x 26.0" x 24.75" (100.9 x 66.04 x 62.86 cm); Frz: 15.5" x 26.0" x 21.0" (39.4 x 66.04 x 53.34 cm)	cCSAus	205 lbs. (93 kg)
25LCEETSA	24.9 cu. ft. (705.1 liters)	Ref: 3 shelves, 3 drawers, 4 door bins; Frz: 2 storage baskets	115V/60hz	69.8" x 32.7" x 37.5" (177.4 x 83.2 x 95.2 cm)	Ref: 40.6" x 30.2" x 29.2" (101.3 x 76.8 x 74.1 cm); Frz: 20.6" x 30.2" x 29.2" (52.3 x 76.8 x 74.1 cm)	cULus	275 lbs (124.7 kg)

In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: thermofisher.com

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: thermofisher.ca

Find out more at thermofisher.com/cold

ThermoFisher
SCIENTIFIC