Thermo Scientific Vanquish – Binary Pump H

Better separations, more results, easier interaction

Thermo Scientific[™] Vanquish[™] UHPLC system is designed to offer:

- Better separations with the power of the system to unveil more compounds than ever before
- More results with throughput, speed and sample capacity to boost workflow productivity
- Easier interaction to make the system a joy to work with

The Vanquish UHPLC system is designed as an integrated UHPLC system, where the pump drives the separation with more power.



Vanquish Binary Pump

Solvent Delivery for Highest Confidence in Peak Identification and Quantification

The Vanquish Binary Pump H was developed to offer more pressure capabilities than ever before, without any tradeoff on durability and robustness. From ultra-fast to extremely shallow gradients at pressures up to 150 MPa, the industry-leading fourth generation SmartFlow[™] pumping technology of the Vanquish system always provides you with unmatched retention time reproducibility and the lowest baseline noise for the highest detection sensitivity.

- Profit from the best harmonization of pumping control and smart fluidics for lowest gradient delays and exceptional gradient profile formation
- Rely on unmatched flow accuracy and precision by nanometer piston motion control
- Enjoy lowest pulsation up to 150 MPa by the Adaptive Thermal Effect Compensation
- Achieve maximum seal and piston lifetime by optimized stroke volume and DLC-coated pistons
- Set up your fluidics all tool-free with Thermo Scientific[™] Viper[™] fingertight fitting technology



| PRODUCT SPECIFICATIONS | |
|--------------------------------------|---|
| Specification | Value |
| Operating Principle | Parallel dual piston with independent piston drives and variable stroke volume |
| Flow Range | 0.001–5 mL/min, in 1 µL/min increments |
| Pressure Range | 5–151 MPa, (50–1517 bar, 700–22,000 psi) |
| Compressibility Compensation | Fully automated, independent of mobile phase composition |
| Flow Accuracy | ±0.1% |
| Flow Precision | <0.05% RSD or <0.01 min SD, whichever is greater |
| Pulsation | <0.4% or <0.2 MPa, whichever is greater; Typically <0.2% or <0.05 MPa, whichever is greater |
| Gradient Formation | High-pressure gradient proportioning |
| Proportioning Accuracy | $\pm 0.2\%$ of full-scale (from 0.2 to 4.0 mL/min and 1 to 99%) |
| Proportioning Precision | <0.15% SD (from 0.2 to 4.0 mL/min and 1% to 99%) |
| Number of Solvent Lines | 2 out of 6 |
| Mixer Volume | 25 μL (default configuration) |
| Solvent Degassing | Built-in, 6 Channels |
| GLP | Predictive Performance functions for scheduling maintenance procedures based on the actual operating and usage conditions of the pump. All system parameters logged in the Thermo Scientific [™] Dionex [™] Chromeleon [™] Chromatography Data System Audit Trail. |
| PC Connection | USB 2.0 3-port-HUB to connect further Vanquish modules |
| I/O Interfaces | 2×6 pin Mini-DIN connectors each having functionality: 1 input, 1 relay out, 1 bidirectional input/output |
| Safety Features | Leak detection and safe leak handling, excess pressure monitoring |
| Wetted Parts | MP35N, DLC, titanium, zirconium oxide (ZrO ₂), sapphire, aluminium oxide (Al ₂ O ₃), PEEK, PTFE, ECTFE, FEP, UHMW polyethylene, perfluoro-elastomer, amorphous fluoropolymer (AF) |
| Biocompatible | Yes, pH range 2–12, buffer and/or chloride concentration up to 1 mol/L |
| Power Requirements | 100–240 V AC, 50/60 Hz, max. 525 W/550 VA |
| Environmental Conditions | 5–35 °C 20–80% RH (non condensing) |
| Dimensions ($h \times w \times d$) | 192 mm \times 420 mm \times 620 mm (7.6 \times 16.5 \times 24.4 in.) |
| Weight | 32 kg (70.5 lbs) |
| | ORDERING INFORMATION |
| Description | Part Number |
| Vanquish Binary Pump H | VH-P10-A |

Optional Mixer for TFA Applications 6268.5120 To order in the U.S., call 1-800-346-6390, or contact the Thermo Fisher Scientific office nearest you. Outside the U.S., order through your local Thermo Fisher Scientific office or

distributor. Refer to the following part numbers.

www.thermofisher.com/chromatography

©2016 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries. This information is presented as an example of the capabilities of Thermo Fisher Scientific products. It is not intended to encourage use of these products in any manners that might infringe the intellectual property rights of others. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

Africa +43 1 333 50 34 0 Australia +61 3 9757 4300 Austria +43 810 282 206 Belgium +32 53 73 42 41 Brazil +55 11 3731 5140 Canada +1 800 530 8447 China 800 810 5118 (free call domestic) 400 650 5118 PS71186-EN 09/16M

 $\begin{array}{c} \textbf{Denmark} & +45\ 70\ 23\ 62\ 60\\ \textbf{Europe-Other} & +43\ 1\ 333\ 50\ 34\ 0\\ \textbf{Finlad} & +358\ 9\ 3291\ 0200\\ \textbf{France} & +33\ 1\ 60\ 92\ 48\ 00\\ \textbf{Germany} & +49\ 6103\ 408\ 1014\\ \textbf{India} & +91\ 22\ 6742\ 9494\\ \textbf{Italy} & +39\ 02\ 950\ 591\\ \end{array}$

Japan +81 6 6885 1213 Korea +82 2 3420 8600 Latin America +1 561 688 8700 Middle East +43 1 333 50 34 0 Netherlands +31 76 579 55 55 New Zealand +64 9 980 6700 Norway +46 8 556 468 00 Russia/CIS +43 1 333 50 34 0 Singapore +65 6289 1190 Sweden +46 8 556 468 00 Switzerland +41 61 716 77 00 Taiwan +886 2 8751 6655 UK/Ireland +44 1442 233555 USA +1 800 532 4752



A Thermo Fisher Scientific Brand