

More antimicrobials, more testing options

Thermo Scientific™ Sensititre™ Standard Veterinary Formularies

Code	Antimicrobial	AVIAN1F	BOPO6F	CMV1BURF	COMPGP1F	COMPGN1F	EQUIN1F	CAMPY*	CMV1AMAF
AMI	Amikacin				16-32	4-32	4-32		
AMOX	Amoxicillin	0.25-16							
AUG	Amoxicillin/ clavulanic acid			2/1-256/128	0.25/0.12-8/4	0.25/0.12-8/4			
AMP	Ampicillin		0.25-16	2-256	0.25-8	0.25-8	0.25-32		0.12-8
AZI	Azithromycin						0.25-4		
FAZ	Cefazolin				2-4	1-32	4-16		
FOV	Cefovecin				0.06-8	0.25-8			
FOX	Cefoxitin								
POD	Cefpodoxime				2-8	1-8			
TAZ	Ceftazidime					4-16	1-64		
XNL	Ceftiofur	0.25-4	0.25-8	0.5-4			0.25-4		0.5-4
LEX	Cephalexin			4-256		0.5-16			
CEP	Cephalothin				2-4				2-16
CHL	Chloramphenicol				8-32	2-32	4-32		
CTET	Chlortetracycline		0.5-8						
CIP	Ciprofloxacin							0.015-64	
CLA	Clarithromycin						1-8		
CLI	Clindamycin	0.5-4	0.25-16		0.5-4			0.03-16	
DANO	Danofloxacin		0.12-1						
DOX	Doxycycline				0.12-0.5	0.25-8	2-16		
ENRO	Enrofloxacin	0.12-2	0.12-2	0.03-4	0.25-4	0.12-4	0.25-2		
ERY	Erythromycin	0.12-4			0.25-4		0.25-8	0.03-64	0.25-4
FFN	Florfenicol	1-8	0.25-8					0.03-64	
GEN	Gentamicin	0.5-8	1,16		4-16	0.25-8	1-8	0.12-32	
IMI	Imipenem				1-4	1-8	1-8		
MAR	Marbofloxacin				1-4	0.12-4			
MIN	Minocycline				0.5-2				
NAL	Nalidixic Acid							4-64	
NEO	Neomycin	2-32	4-32						
NIT	Nitrofurantoin				16-64				
NOV	Novobiobin	0.5-4							
ORB	Orbifloxacin					1-8			
OXA+	Oxacillin +2%NaCL				0.25-2		0.25-4		2-4
OXY	Oxytetracycline	0.25-8	0.5-8						
PEN	Penicillin	0.06-8	0.12-8		0.06-8		0.06-8		0.12-8
P/N	Penicillin/ novobiocin								1/2-8/16
P/T4	Piperacillin/ tazobactam					8/4-64/4			
PIRL	Pirilmycin								0.5-4
PRA	Pradofloxacin				0.25-2	0.25-2			
RIF	Rifampin				1-2		1-4		
SPE	Spectinomycin	8-64	8-64						
STR	Streptomycin	8-1024							
SDM	Sulphadimethoxine	32-256	256						32-256
STZ	Sulphathiazole	32-256							
TEL	Telithromycin							0.015-8	
TET	Tetracycline	0.25-8		2-128	0.25-1	4-16	2-8	0.06-64	1-8
TIA	Tiamulin		0.5-32						
TIC	Ticarcillin						8-64		
TIM2	Ticarcillin/ clavulanic acid						8/2-64/2		
TIL	Tilmicosin		4-64						
SXT	Trimethoprim/ sulfamethoxazole	0.5/9.5-2/38	2/38	2/38-8/152	2/38-4/76	0.5/9.5-4/76	0.5/9.5-4/76		
TUL	Tulathromycin		1-64						
TYLT	Tylosin tartrate	2.5-20	0.5-32						
VAN	Vancomycin				1-16				

*Requires visual interpretation. †Not available in the U.S.

Code	Antimicrobial	CMV3AGPF	CMV3AGNF	JO-EYE2	EUCAMP2 [†]	EUST [†]	EUVENC [†]	EUVSEC [†]	EUVSEC2 [†]
AMI	Amikacin			16-32					
AMP	Ampicillin		1-32				0.5-64	1-64	
AZI	Azithromycin		0.12-16					2-64	
BAC	Bacitracin			2-4					
FAZ	Cefazolin			8-16					
FEP	Cefepime								0.06-32
FOT	Cefotaxime							0.25-4	0.25-64
F/C	Cefotaxime/ clavulanic acid								0.06/4- 64/4
FOX	Cefoxitin		0.5-32			0.5-16			0.5-64
TAZ	Ceftazidime							0.5-8	0.25-128
T/C	Ceftazidime/ clavulanic acid								0.12/4- 128/4
XNL	Ceftiofur		0.12-8	2-4					
AXO	Ceftriaxone		0.25-64						
CHL	Chloramphenicol	2-32	2-32	4-16		4-64	4-128	8-128	
CIP	Ciprofloxacin	0.12-4	0.015-4	1-4	0.06-8	0.25-4	0.12-16	0.015-8	
CLI	Clindamycin					0.12-4			
COL	Colistin							1-16	
DAP	Daptomycin	0.25-16					0.25-32		
DOX	Doxycycline			0.12-2					
ETP	Ertapenem								0.015-2
ERY	Erythromycin	0.25-8		0.5-4	1-128	0.25-8	1-128		
FUS	Fusidate					0.5-4			
GEN	Gentamicin	128-1024	0.25-16	2-8	0.12-16	1-16	8-1024	0.5-32	
IMI	Imipenem								0.12-16
KAN	Kanamycin	128-1024				4-64			
LIN	Lincomycin	1-8							
LZD	Linezolid	0.5-8				1-8	0.5-64		
MERO	Meropenem							0.03-16	0.03-18
MXF	Moxifloxacin			0.5-1					
MUP	Mupirocin					0.5-2, 256			
NAL	Nalidixic Acid		0.5-32		1-64			4-128	
NEO	Neomycin			4-8					
NIT	Nitrofurantoin	2-64							
OFL	Ofloxacin			0.12-1					
OXY	Oxytetracycline			0.5-4					
PEN	Penicillin	0.25-16				0.12-2			
POL	Polymixin B			5-10					
SYN	Quinupristin/ dalfopristin	0.5-32				0.5-4	0.5-64		
RIF	Rifampin					0.016-0.5			
STR	Streptomycin	512-2048	2-64		0.25-16	4-32			
SMX	Sulfamethoxazole					64-512		8-1024	
FIS	Sulfisoxazole		16-256						
TEI	Teicoplanin						0.5-64		
TRM	Temocillin								0.5-64
TET	Tetracycline	1-32	4-32		0.5-64	0.5-16	1-128	2-64	
TIA	Tiamulin					0.5-4			
TIC	Ticarcillin			16-64					
TGC	Tigecycline	0.015-0.5					0.03-4	0.25-8	
TOB	Tobramycin			4-16					
TMP	Trimethoprim					2-32		0.25-32	
SXT	Trimethoprim/ sulfamethoxazole		0.12/2.38-4/76	2/38					
TYLT	Tylosin tartrate	0.25-32							
VAN	Vancomycin	0.25-32				1-16	1-128		

AVIAN1F: avian and poultry-specific formulary
BOPO6F: bovine and porcine-specific formulary containing FDA-approved food animal compounds
CAMPY*: *Campylobacter* spp.-specific formulary
CMV1AMAF: mastitis-specific formulary containing FDA-approved food animal compounds
CMV3AGNF: Gram negative isolate formulary
CMV3AGPF: Gram positive isolate formulary
CMV1BURF: dual isolate urinary isolate-specific formulary
COMPGP1F: companion animal-specific antimicrobics for Gram positive isolates

*Requires visual interpretation. †Not available in the U.S.

For veterinary use only. This list is to be used for information only, and may be updated at any time by Thermo Fisher Scientific. Contact your local Thermo Fisher Scientific Microbiology sales representative or distributor to obtain the most current list.

thermoscientific.com/vetmicro

© 2015 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

Contact Information:
microbiology@thermofisher.com
USA +1 800 255 6730
International +44 (0) 1256 841144

991-228
LT2162A
October 2015

COMPGN1F: companion animal-specific antimicrobics for Gram negative isolates
EQUIN1F: equine-specific formulary
EUCAMP2[†]: two isolate *Campylobacter* spp.-specific format
EUST[†]: Staphylococci-specific plate format
EUVENC[†]: *Enterococcus* spp.-specific plate format
EUVSEC[†]: Salmonella and *E. coli*-specific format
EUVSEC2[†]: ESBL-specific plate format
JO-EYE2: two isolate, 96-well microtitre plate for breakpoint testing of topical compounds

