

**Thermo Scientific Barnstead Smart2Pure UV 6LPH Water Purification System  
A & E Specification Sheet**

Lab water purification system capable of producing between 1 – 40 L/day of Type 1 ultrapure water on demand from a tap/potable feed water supply

**PART 1 – GENERAL**

**1.1 DESIGN AND PERFORMANCE CRITERIA**

- A. Water purification system must provide 18.2 megohm quality (Type 1) water to be utilized in a laboratory environment. Type 1 water quality meets standards as defined by ASTM D1193-6, ISO 3696 and CLSI™-CLRW.
- B. Water purification system will be capable of delivering up to 40L per day at a production rate of 6LPH and a flow rate of 1 liter per minute using tap/potable feed water as the supply water.
- C. Water purification system must function as one component with a built-in storage reservoir. The water purification system must be able to be mounted on the wall or bench.
- D. The system must also have built in a product water resistivity monitor.

**1.2 SUBMITTALS**

Product Brochure  
Water Purification System Operating Manual (includes installation instructions)  
Product Guidelines for Site Installation  
Drawings

**1.3 QUALITY ASSURANCE**

- A. Each water purification system will be certified by CE and CSA for electrical safety and integrity.

**1.4 QUALIFICATION**

- A. Manufacturer – Company must have 10 years documented experience in the construction of water purification systems.
- B. Water Purification System – Shall be CE and CSA certified and meet ASTM D1193 standards.

**1.5 WARRANTY**

- A. Manufacturer's warranty against defects in material and workmanship covering parts and labor must be available for a period of one year. Standard exceptions for cartridges, filters, and lamps shall apply.

## **PART 2 – PRODUCT**

### **2.1 MANUFACTURER**

A. Thermo Scientific Barnstead Smart2Pure UV 6LPH water purification system – **50129885**

### **2.2 WATER PURIFICATION SYSTEM PRODUCT WATER SPECIFICATIONS**

- A. Ultrapure water flow rate of 1L/minute
- B. Type 2 product water must have a resistivity of 10-15 megohms-cm at 25 °C
- C. Type 1 product water must have a resistivity of up to 18.2 megohms-cm at 25°C and:
  - a. Less than 5 ppb TOC (Total Organic Carbon) in the product water
  - b. Bacterial counts less than 1 CFU/ml

### **2.3 WATER PURIFICATION SYSTEM PERFORMANCE REQUIREMENTS**

- A. The system must be able to produce both type 1 and type 2 quality water and both types must be accessible by the end-user to meet different application requirements. Systems producing Type 1 and RO quality water are not acceptable.
- B. Dispensing of type 1 water must be from the front of the water system with a variable flow control knob.
- C. Dispensing ports for type 2 water must be from the side of the unit to allow for bench mounting. Dispensing ports on bottom of the reservoir is not acceptable.
- D. An optional hand dispenser must be available for the dispensing of type 2 water from the system.
- E. System must come with built-in 6L reservoir for the storage of the type 2 water. External reservoirs are not acceptable.
- F. System display must have adjustable angle display to make the display easy to read from any angle.
- G. System display should provide all system status data plus access to user menu.
- H. The system will include a UV lamp with a two-year lifespan that will emit both 185 nm and 254 nm wavelengths, designed to ensure organic removal as well as maintaining a bacteria-free environment.
- I. The system will automatically switch to “Interval” operation after the reservoir is completely filled.
- J. The system will automatically recirculate for 14 mins after every 16 min of being idle to ensure product water is always fresh and ready for use.
- K. Systems cartridges must be able to be removed / replaced with quick disconnect fittings with no threads, screws or other mechanisms required to change cartridges.
- L. System cartridges must be two discreet canisters. One cartridge containing the RO membrane and carbon and the second cartridge containing the resin required to produce type 1 water. One housing for all is not acceptable.
- M. An absolute 0.2µm polysulfone membrane filter is required as the final purification step as the water is being dispensed. The final filter will be sterilizable using an autoclave.
- N. Temperature measurements are made by a platinum chip sensor with  $\pm 0.1^\circ$  C accuracy.

## 2.4 – ACCESSORIES

### A. REQUIRED

- a. **09.4003** – 1 micron pretreatment filter to protect RO membrane from particulate damage

### B. OPTIONAL

- a. **09.4001** – 5 micron filter and hardness stabilizer to protect RO membrane from scaling in areas where high levels of hardness occur
- b. **09.2212** – Wall mounting bracket to affix system to wall
- c. **50138221** – Hand dispenser

### C. REPLACEMENT CONSUMABLES

- a. **09.1020** - Ultrapure polishing cartridge
- b. **09.1002** - UV lamp
- c. **09.1003** - 0.2 micron final filter
- d. **09.2006** – RO membrane with integrated carbon pretreatment

## ADDITIONAL SPECIFICATIONS

DIMENSIONS (System)	12" W x 15.47" D x 21.5" H (305mm x 400mm x 545mm)
ELECTRICAL REQUIREMENTS	100 – 240 V, 50/60 Hz, 2-1A, up to 5 ft from unit
WATER CONNECTIONS	¾" NPT with manual shut off valve recommended
MIN/MAX INLET PRESSURE	15 – 85 PSI (0.1 – 6 bar)
RECOMMENDED FEED TEMPERATURE	2 – 35°C
RECOMMENDED FEED WATER TYPE	Tap/Potable Water
DRAIN	An atmospheric drain must be available within 5 feet of the final mounting location