


Slide-A-Lyzer[®] Dialysis Cassette and MINI Unit Dimensions

TR0054.2

Slide-A-Lyzer Dialysis Cassettes



Inch dimensions of Slide-A-Lyzer Dialysis Cassettes

<u>Slide-A-Lyzer Cassette Size</u>	<u>Cassette Face (Corner length)</u>	<u>Cassette Thickness</u>	<u>Gasket Face (Corner length)</u>	<u>Gasket Thickness = Window thickness</u>	<u>Window Face</u>
0.1-0.5 ml	1.625 × 1.625 (0.25)	0.295	1.237 × 1.237 (0.295)	0.125	0.5 × 0.5
0.5-3 ml	2.625 × 2.25 (0.625)	0.295	2.0 × 1.25 (0.625)	0.125	1.375 × 1.0
3-12 ml	3.75 × 2.25 (0.312)	0.437	3.25 × 1.75 (0.312)	0.235	2.5 × 1.0
12-30 ml	4.562 × 3.5 (top = 1.625) (bottom = 0.687)	0.5	2.875 × 3.125 (0.312)	0.295	2.5 × 2.125

Centimeter dimensions of Slide-A-Lyzer Dialysis Cassettes


<u>Slide-A-Lyzer Cassette Size</u>	<u>Cassette Face (Corner length)</u>	<u>Cassette Thickness</u>	<u>Gasket Face (Corner length)</u>	<u>Gasket Thickness = Window thickness</u>	<u>Window Face</u>
0.1-0.5 ml	4.1 × 4.1 (0.65)	0.75	3.1 × 3.1 (0.75)	0.32	1.25 × 1.25
0.5-3 ml	6.7 × 5.7 (1.5)	0.75	5.5 × 4.5 (1.5)	0.32	3.5 × 2.5
3-12 ml	9.5 × 5.7 (0.8)	1.0	4.5 × 8.2 (0.8)	0.60	6.3 × 2.5
12-30 ml	11.6 × 9.3 (top = 4.1) (bottom = 1.8)	1.3	7.4 × 8.0 (0.8)	0.75	5.6 × 6.1

Float Buoys

66430	Single Cassette Buoys (white) for 0.5 and 3 ml cassette sizes: 5 × 3.2 cm (2.5 cm tall)
66431	Carousel Buoy (white) for 0.5 and 3 ml cassette sizes: 14 × 11.5 cm (3 cm tall)
66432	Single Buoy (gray) for 3-12 ml cassette size: 6.4 × 3.8 cm (2.5 cm tall)
69588	Float Buoy for 25 MINI Units:

Slide-A-Lyzer MINI Dialysis Units

Dimensions in millimeters (mm)



- * Hanging height in a microcentrifuge tube
- ** Tapered (8.5 mm at bottom, 9 mm above)

Current versions of product instructions are available at www.thermo.com/pierce. For a faxed copy, call 800-874-3723 or contact your local distributor.

© 2008 Thermo Fisher Scientific Inc. All rights reserved. Unless otherwise indicated, all trademarks are property of Thermo Fisher Scientific Inc. and its subsidiaries. Printed in the USA.