

# QuantStudio Dx Real-Time PCR Instrument

- Performance you can trust.
- Security you need.
- Flexibility you want.
- A diagnostic platform that can grow with you.



## Introduction

The Applied Biosystems™ QuantStudio™ Dx Real-Time PCR Instrument addresses the challenges of a clinical laboratory by combining multiple system capabilities in a single footprint without sacrificing simplicity, and by offering a platform that can accommodate a growing list of in vitro diagnostic (IVD) assays and new assay development.

## Instrument

The QuantStudio Dx Real-Time PCR Instrument is designed to deliver the proven reliability, sensitivity and accuracy you expect from Applied Biosystems™ instruments, with specific features designed for the molecular diagnostic laboratory environment. The QuantStudio Dx instrument, when operated in Test Development Mode, leverages proven design elements from eight generations of Applied Biosystems real-time PCR systems and incorporates the flexibility of four user-interchangeable qPCR blocks (96-well standard, Fast 96-well, 384-well and qPCR microfluidic card), making it easier to get the high-quality results you need.

## Software

**The QuantStudio Dx Software supports the demands of a diagnostic workflow to streamline your laboratory processes**

- IVD tests are controlled by a Test Definition Document (TDD), with predefined run and analysis parameters to help reduce setup time and programming effort.
- Reagent and sample information can be tracked by assay for quality control purposes.
- Reagents and other critical information can be entered by barcode, and sample information can be uploaded (e.g., from Microsoft™ Excel™ files) to minimize data entry errors.
- The QuantStudio Dx instrument can be configured to provide results to a laboratory information system (LIS), minimizing staff workloads.

## Test Development Mode

- Supports clinical research applications and assay development.
- Allows laboratories to develop assays.
- Provides additional applications to customize protocols and analysis.

## Features that help you comply with the requirements of accrediting bodies

<b>Maintenance and calibration reports</b>	Documents that the QuantStudio Dx Real-Time PCR Instrument has been maintained and calibrated to vendor specifications. Records are updated automatically with maintenance and calibration events and can be printed on demand.
<b>Reagent tracking</b>	Stores and archives information about reagents used with each test, including lot number and expiration date, with each run. Archived files can be retrieved when required, to track samples that were tested with a given set of reagents.
<b>Sample tracking</b>	Captures critical sample data that can be customized to fit the laboratory's needs. Tracks information such as name, accession number, and sample type. Enables laboratories to more easily track samples associated with a particular plate, set of reagents, run date/time, and data files.

## Hardware specifications

<b>Block change design</b>	Block is changed from the front of the instrument in less than 1 minute; no tools required
<b>Temperature uniformity</b>	±0.5°C
<b>Run time</b>	For IVD tests, refer to package inserts for specific run times Run times using Test Development Mode will vary depending on the assay type, block, and reagents used. Examples: ~35 min for 384-well, ~30 min for 0.2mL 96-well and 0.1mL Fast 96-well, and <1 hr for Applied Biosystems™ TaqMan™ Array Cards* (when using TaqMan Fast Advanced Master Mix*)
<b>Demonstrated sensitivity</b>	Down to 1 copy (see package inserts for IVD test performance specifications)
<b>Dynamic range</b>	Up to 9 logs of linear dynamic range
<b>Supported applications</b>	Standard curve, comparative C <sub>t</sub> genotyping, HRM (with license), melt curve, gene expression, qualitative and quantitative assays
<b>Resolution</b>	Detect as little as 1.5-fold change in target quantities in singleplex reaction (see package inserts for IVD test performance specifications)
<b>Supported blocks and reaction volumes</b>	96-well standard (10–100µL), Fast 96-well** (10–30µL), 384-well (5–20µL), qPCR microfluidic cards (~1µL)
<b>Excitation/detection wavelengths</b>	6 excitation (450–670nm), 6 emission (500–720nm)
<b>Security and auditing features</b>	Assists with 21 CFR Part 11 compliance
<b>Power</b>	100–240V, 50/60Hz
<b>Remote monitoring by user</b>	Ability to monitor up to 10 instruments at a time
<b>Remote diagnostics</b>	Optional Smart Monitoring Service for remote instrument diagnostic monitoring (Available in selected regions. Check with your local representative.)
<b>Remote notification</b>	Sends email to user when run is started, stopped, or aborted
<b>Data export format</b>	Select .txt or Microsoft™ Excel™ file formats
<b>Dimensions (W x D x H)</b>	53 x 70 x 75 cm
<b>Weight</b>	70 kg

\* TaqMan products are For Research Use Only. Not for use in diagnostic procedures.

\*\* Only the Fast 96-well plate format is available in IVD mode in the US.

The QuantStudio Dx Real-Time PCR Instrument with QuantStudio Dx Software is intended for in vitro diagnostic use by trained laboratory technologists in combination with nucleic acid reagent kits/tests manufactured and labeled for diagnostic use on this instrument.

Learn more at [thermofisher.com/quantstudiodx](http://thermofisher.com/quantstudiodx)

**ThermoFisher**  
SCIENTIFIC

**For In Vitro Diagnostic Use. Available in the US and other selected countries.** ©2015 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. TaqMan is a trademark of Roche Molecular Systems, Inc., used under permission and license. Microsoft and Excel are trademarks of Microsoft Corporation. **CO016367 0815**